



# APM101

Digital Paging Microphone

## ► Features

- Reliable & Versatile
- APM configuration software included
- Both analogue & digital audio transfer
- Modular structure
- Voice File Interface
- Fitted with cardioid condenser capsule
- 1 zone selectable
- Built-in compressor/limiter

## ► Applications

- Public buildings
- Fire departments
- Warehouses
- Business offices
- Sports sites



The APM101 is a one zone fully digitally controlled and monitored paging microphone which can be used for a wide variation of paging purposes, such as priority calls, dispatching and evacuation.

It is designed to be used in combination with AUDAC Digital Matrix Systems, but in combination with the ARU intelligent relay units, it can be applied to any existing sound system.

Due to the freely programmable and modular structure, it can be used for a wide variation of applications ranging from simple & small to the most complex applications at users specific requirements, creating an infinite number of configuration possibilities.

The paging console is fitted with a cardioid gooseneck microphone, and the operation of the system is completely digitally monitored from microphone cell to signal amplifier to detect any malfunction or failure in the system. This is necessary to ensure a 100% reliability of the system in case of an emergency call.

This microphone has only one button on the control panel with the "PTT" (Push To Talk) function.

Including windscreen.

## ► Specifications

SYSTEM SPECIFICATIONS	
Max power consumption	4.8 W
Impedance microphone	200 Ohm
Sound pressure Max W/1m	120 dB
Frequency response -3dB	150 Hz - 20 kHz
Sensitivity Microphone (1V/Pa)	-44 dB @ 1 kHz +/- 3dB
Power Supply	24 V DC
PRODUCT FEATURES	
Dimensions (Width x Height x Depth)	120 x 55 x 190 mm
Weight net	1.1 Kg
Construction	Steel
Connector	RJ45
Digital Control	RS485
Standard Data Bus	RS485
Microphone Type	Electret
Polar Pattern	Cardioid
Colour	Grey (RAL7016)
Output Level	Programmable
Paging Zones	1
SHIPPING & ORDERING	
Packaging	Carton box
Shipping weight & volume	2 Kg - 0.0012 Cbm

\*AUDAC reserves the right to change specifications without notice: this is part of our policy to continually improve our products